

Issue: 08/2023

Tel.: +49 (0) 60 71 - 928 4000

Fax: +49 (0) 60 71 - 928 4019

E-Mail: info@texit.de

Technical Data Sheet

Product-Line: HTX-KM-DET Material: Polyether based TPU TEXIT-Material-Code: TMC-1154

Material data:

Description

Cable Markers extruded from Polyether based TPU compound. Optimised to the operation of the most usual metal detectors and x-ray detectors. The compounds meets requirements for food contact compliant with EU and FDA requirements. Compound is hydrolysis "No break down in water" and micro organism resistant.

In food production with open production processes it is advisable to use materials that are easily detectable. TEXIT offers products that are simple to detect. They make an important contribution to quality management for the food industry, particularly when following the HACCP approach.

The labels are fixed to the cable or wire using detectable cable ties at both ends. The product is supplied as an all-in-one construction, where the extruded material also functions as the carrier.

The markers are partially perforated for easy picking after printing and supplied on rolls for thermal transfer printing.

Standard colours

blue (RAL 5012 -)

Material

Polyether based TPU

Continuous Operating temperature

-25°C up to +105°C (-13°F to 221°F)

Gueterstrasse 2, DE-64807 Dieburg



Technical Data Sheet

Page 2 of 12

TMC-1154/TMC-1154

Resistance to solvents

Customer Tests on-Site Novadan Fluid Test Report

Ribbon: FTI-Y

Printer recommended

- TEXIT DRU-TX4/300
- TEXIT DRU-TX4M/300
- TEXIT DRU-TEP5/300

Ribbon recommended

- FTI-Y

Flammability Standard

Class HB - UL94

Standards

FDA "Food & Drug" 21 CFR -

GRAS

"generally accepted as safe"

Regulation (EU) no 10/2011

Plastics inteded to com into contact with food

Storage

- Cool and dry in original packaging
- Recommended temperature at +10°C to +25°C and 45-55% relative humidity

Applications

Developed to be used in Food Industry and other Industries requiring detection through metal detectors or X-ray equipment

Tel.: +49 (0) 60 71 - 928 4000 Fax: +49 (0) 60 71 - 928 4019

E-Mail: info@texit.de

Gueterstrasse 2, DE-64807 Dieburg



Technical Data Sheet

Page 3 of 12

TMC-1154/TMC-1154

Tel.: +49 (0) 60 71 - 928 4000 Fax: +49 (0) 60 71 - 928 4019 E-Mail: <u>info@texit.de</u>

General Values for TPU Identification Products:

Physical properties				
Properties	Test Method	Typical Value		
Stress at 20 % strain	DIN 53504	12 MPa		
Stress at 100 % elongation	DIN 53504	16 MPa		
Stress at 300% elongation	DIN 53504	34 MPa		
Density	DIN 53479	1,52 g/cm3		
Tensile Strength	DIN 53504	36 MPa - Using standardized test specime		
Elongation @ break	DIN 53504	450 %		
Charpy notched impact strength, -30°C	DIN EN ISO 179	No break		
Charpy notched impact strength, 23°C	DIN EN ISO 179	No break		
Tensile Strength after storage in water at 80°C for 42 days	DIN 53504	20MPa		
Compression set at room temperature, 24h	DIN EN ISO 815	30%		
Compression set at 70°C, 24h	DIN EN ISO 815	50 %		
Tear Strength	DIN 53515	110 N/mm		
Abrasion resistance	DIN 53516	30mm3		
Shorehardness	DIN 53505	Shore D 55		

Thermal properties			
Properties	Test Method	Typical value	
Glass transition temperature, 10°C/min	ISO 11357-1/-2	-30°C	
Burning behaviour at 0.75 mm nom thickness	UL94	Class HB	
Melting temperature 10°C/min	ISO 11357-1/-3	137°C	
Short Max working temperature		105°C	

Gueterstrasse 2, DE-64807 Dieburg



Technical Data Sheet

Page 4 of 12

TMC-1154/TMC-1154

Tel.: +49 (0) 60 71 - 928 4000

Fax: +49 (0) 60 71 - 928 4019

E-Mail: info@texit.de

Environmental			
Properties	Test Method	Typical value	
UV-A 340 nm 1000 hours Light 60 ° irradiation 0.76 W/m² power	Visual Inspection	No creasing or cracking - NOT TESTED	
duration 8 hours - Spray duration 15 min Condensation 50 ° duration 3,45 hour	Mark Adherence	Good contrast and visibility - NOT TESTED	
		NO UV TEST - NOT TESTED	

SVHC	Test Method	Typical value
Substances Of Very High Concern.	Article 57(f) of Regulation (EC) No	No content
DEHP (Bis(2-ethyl(hexyl)phtalat).	1907/2006	

Chemical properties

Solvents resistance

No degradation of the HTX-KM-DET TPU products occurs, however, according to the solvent class a variable degree of swelling and consequent reduction in tensile strength (after evaporation of the solvents, the tensile strength recovers approx. its original value).

Methanol should be considered more as a chemical reagent than as a solvent. TPU is soluble in some solvents. As test procedure, 5A test rods (DIN EN ISO 527-2) were immersed in the solvent for three weeks at 23° C, and tested for tensile strength are rounded values.

Code	Test fluid	Swelling	Reduction of tensile strength
Aliphatic Hydrocarbons	Pentan	10	20
	Cyclohexan	22	10
	Isooctan	7.5	none

HTX-KM-DET behave similarly in other aliphatic and cyclo-aliphatic hydrocarbons such as methane, ethane, propane, butane, hexane, octane, petroleum ether, paraffin oil, diesel oil and kerosine (although additives can present problems)



Technical Data Sheet

Page 5 of 12

TMC-1154/TMC-1154

Aromatic Hydrocarbons		Toulene		65		50	
Other aromatic hydroca	rbons suc	ch as benzene a	nd xylene	nave a s	similar affect.		
Aliphatic Esters	Ethyl A	cetate			70	75	
Other short-chained est	ers such	as butyl acetate	and amyi	acetate	have a similar a	nffect	
Aliphatic Ketones	Methyl	Ethyl Ketone			130	90	
Other short-chained alip MIBK have a similar affo		ones such as ac	etone and	methyl	isobutyl ketone	=	
Aliphatic Halogenated Hydrocarbons, 1 C-atom 1 C-atom and higher	Chlorof Tetrach	Ethyle Chloride orm lloroethylene roethane*			190 75	95 Prectically dissolved 54	
*Other aliphatic haloger	nated hyd	lrocarbons with	2 C-atoms	and hig	her have a simi	lar affect	
Aromatic Halogenated Hydrocarbons	Chlorot	enzene			110	60	
Other aromatic halogen	ated hydi	ocarbons have	a similar a	fect			
ASTM-Oils acc. to ASTM D 471-06**	IRM 90	1 at 100 °C 1 at 100 °C 2 at 100 °C	500 1000 500	h	1 1 9	6 14 4	
	IRM 90 IRM 90	2 at 100 °C 3 at 100 °C 3 at 100 °C	1000 500 1000	h h	10 18 20	5 8 30	

Tel.: +49 (0) 60 71 - 928 4000 Fax: +49 (0) 60 71 - 928 4019 E-Mail: <u>info@texit.de</u>

Gueterstrasse 2, DE-64807 Dieburg



Technical Data Sheet

Page 6 of 12

TMC-1154/TMC-1154

Agents Dissolving TPU	Tetrahydrofurane	dissolved	dissolved
	Dimethyl Formamide (DMF)	dissolved	dissolved
	Dimethyl Acetamide	dissolved	dissolved
	N-Methyl Pyrrolidone (NMP)	dissolved	dissolved
	Dimethyl Sulphoxide (DMSO)	dissolved	dissolved
	Pyridine	dissolved	dissolved

Code	Test fluid	Swelling	Reduction of tensile strength
Alcohols and Fuels	Methanol Ethanol	28 33	6 14
	Iso-Propanol Benzyl Alcohol	30 not measureable	4 partly dissoved
	Ethylen Glycol Glycerine	4 none	15 none
FAM Test Fluids acc. to DIN 51 604*	Test Fluid A Test Fluid B Test Fluid C	67 68 43	60 74 70
Diesel Fuel Biodiesel Fuel RME @ 60°C	Diesel Fuel Biodiesel Fuel	11 27	none 21
	Fuel A = Iso-Octane	7.5	none
	Fuel B = Iso-Octane Touene 70% / 30%	25	36
Fuel Types ASTM D 471	Fuel C=Iso-Octane Toluene 50% / 50%	38	44
	Fuel D=Iso-Octane Toluene 60% / 40%	31	44

 $[\]ast$ DIN 51 604, 03.1984, is the standard, etablished by FAM to assess the resistance of plastic materials to automotive fuels.

(FAM = Fachausschuß Mineral- und Brennstoffnormung-Professional committee for standardization of fuel stuffs)

(ASTM = American Society for Testing and Materials)

Test fluid A consists of: 50.0 % by volume toluene 30.0 % by volume iso-octane 15.0 % by volume di-isobutylene 5.0 % by volume ethanol

Test fluid B consists of: 42.0 % by volume toluene 25.5 % by volume iso-octane 13.0 % by volume di-isobutylene 15.0 % by volume methanol 4.0 % by volume ethanol 0.5 % by volume water

Test fluid C consists of: 20.0 % by volume toluene 12.0 % by volume iso-octane 6.0 % by volume di-isobutylene 58.0 % by volume methanol 2.0 % by volume ethanol 2.0 % by volume water

E-Mail: info@texit.de

^{**} The IRM reference oils are mineral oils with different paraffin and aromatics contents. The formerly used ASTM oils 1, 2 and 3 were replaced by the IRM oils 1, 2 and 3 owing to health risks, and are no longer available. The IRM oils 1, 2 and 3 are very similar in terms of their characteristics, but not identical.



Technical Data Sheet

Page 7 of 12

TMC-1154/TMC-1154

Tel.: +49 (0) 60 71 - 928 4000

Fax: +49 (0) 60 71 - 928 4019

E-Mail: info@texit.de

Information on EU No. 10/2011

PLASTICS MATRIALS AND ARTCLES INTENDED TO COME IN CONTACT WITH FOOD

Based on our investigations, experiences and the information provided to us by our raw material suppliers, the polymer compound

HTX-KM-DET Light Blue

complies with EU regulations related to plastic materials intended to come into contact with food EU Regulations:

Regulation 1935/2004 of of 27th of October, Commission Directive 2002/72/EC of 6th of August, corrected on 13th February and further amendments: 2004/1/EC of 6th January, 2004/19/EC of 1st March, 2005/79/EC of 18th November, 2007/19/EC of 30th March, 2008/39/EC of 6th March, 975/2009/EC of 19th October and 10/2011/EC of 1st of May.

All raw materials and additives used to produce the grade are included in the positive lists (Annex II and III). Concerning SML (specific migration limit) and dual-use additives, referred to Annex VI, point (5), migrations tests have to be made at the end parts by the distributor of the parts, in order to guarantee the specific and total migration limit values. The global migration limit is established in 10 mg/dm2.

This information does not cover the ulterior changes in the composition of the material by adding other substances.

This information does not exime the end user of the material to make sure that the final product obtained is in accordance to the legal migration levels and the regulation EU No.10/2011.

The information given above has been compiled carefully and represents the state of our knowledge at issue date. If not otherwise stated, this information is valid for two years after the issue date.



Technical Data Sheet

Page 8 of 12

TMC-1154/TMC-1154

Information on FDA 21 CFR - GRAS (Generally accepted as safe)

PLASTICS MATRIALS AND ARTCLES INTENDED TO COME IN CONTACT WITH FOOD

Based on our investigations, experiences and the information provided to us by our raw material suppliers, the polymer compound

HTX-KM-DET Light Blue

complies with FDA 21 CFR regulations related to plastic materials intended to come into contact with food EU Regulations:

All raw materials and additives used to produce the grade are used in accordance with FDA 21 CFR or are listed as GRAS (generally accepted as safe).

The corresponding sections are §§

175.105

177.1680

177.2600

186.1374

178.3297

174.5

174.6

175.105

176.170

This information does not cover the ulterior changes in the composition of the material by adding other substances.

This information does not exime the end user of the material to make sure that the final product obtained is in accordance to the legal migration levels and the regulation EU No.10/2011.

The information given above has been compiled carefully and represents the state of our knowledge at issue date. If not otherwise stated, this information is valid for two years after the issue date.

Tel.: +49 (0) 60 71 - 928 4000 Fax: +49 (0) 60 71 - 928 4019

E-Mail: info@texit.de



Technical Data Sheet

Page 9 of 12

TMC-1154/TMC-1154

Tel.: +49 (0) 60 71 - 928 4000

Fax: +49 (0) 60 71 - 928 4019

E-Mail: info@texit.de

Information on AP 89/1 EU regulation -

COLORANTS USED IN THE MANUFACTURE OF MATERIALS AND ARTICLES INTENDED FOR FOOD CONTACT APPLICATIONS IN THE EUROPEAN UNION (EU)

The cable identification products are made of detectable polyether based TPU are intended for use for cable identification on food processing, packing quipment, electrical control panels, found in contiguity of food processing and packing operations.

Based on our investigations, experiences and the information provided to us by our raw material suppliers, the polymer compound CMX-DET Light Blue complies with AP89 regulations related to plastic materials intended to come into contact with food EU regulations.

Since conditions of use and application of the products are outside Texit control, Texit gives no guarantees, warranties and assumes no liability whatsoever for any loss, damage or expense arising from or in connection with the use of this information.

The information given above was compiled carefully and represents the state of TEXIT knowlegde and results of our investigation at issue date. The information are based on the data given by our raw material suppliers. This information does not cover the ulterior changes in the composition of the material by adding other substances.

Gueterstrasse 2, DE-64807 Dieburg



Technical Data Sheet

Page 10 of 12

TMC-1154/TMC-1154

Tel.: +49 (0) 60 71 - 928 4000

Fax: +49 (0) 60 71 - 928 4019

E-Mail: info@texit.de

Information examination detectability by metaldetectors & X-ray

Based on our investigations, experiences and the information provided to us by our testing lab.

HTX-KM-DET Light Blue

Study results by means of a metal detector system, the amplitude and phase signals of the present samples were measured. The following figure shows an example of the amplitude and phase signals of a metal ball made of non-ferrous metal (brass) with a diameter of 4mm.




Figure 1 amplitude and phase signal of a metal ball 4mm Non-Ferrous. roughly corresponds to the behavior that the respective parts produce in a metal detector (300Khz) without product compensation.

The following table lists the results of the measurements. Each sample was assigned an equivalent metal ball, i.e. this sphere roughly corresponds to the behavior that the respective parts produce in a metal detector (300Khz) without product compensation. A high product effect by e.g. a high intrinsic conductivity of the food can change the situation greatly. The determined aluminum spheres correspond to the behavior of the test specimens in the X-ray beam at 60 KV. The following table lists the results of the measurements. Each sample was assigned an equivalent metal ball, i.e. this sphere

Sample Description	Equivalent Non-FE sphe- re metal detector for the tested sample	Equivalent aluminium sphere X-ray detector for the tested sample
Foil grey d=0,7mm 6x6x6 mm movement across	ca. 1,7mm	
Foil grey d=0,7mm 10x10x10 mm move- ment across	ca. 2,2 mm	ca. 0,5-0,7mm

Gueterstrasse 2, DE-64807 Dieburg



Technical Data Sheet

Page 11 of 12

TMC-1154/TMC-1154

Related Standardards & Test Methods	
Document	Description
FDA "Food & Drug" Code of Federal Regulations (21 CFR, 182-186) - GRAS "General Recognised As Safe"	Substances generally recognized as safe (GRAS) can be safely used as components of articles that contact food under conditions of good manufacturing practice. A list of GRAS notices with FDA's response can be searched in SCOGS data base. Please note that not all substances that are GRAS are listed in 21 CFR or covered by a GRAS notification.
Regulation (EU) No. 10/2011	Regulation (EU) No. 10/2011 - The monomers as well as the other starting substances, additives and polymer production aids used in the manufacture of these products are listed in annex I (Union List) with the following specific restrictions. 2,6-Di – tet-butyl-p-cresol (BHT) : SML = 3mg/kg food, dual use additive. No Content
Specific Migration Limit	The specific migration limit (SML) is the maximum permitted quantity of a specific substance that can migrate from a food packaging material or food container into food. It is a safety limit derived from toxicological studies. Reliable analytical methods are needed to identify the presence of these substances in food (or food simulants). It is usually expressed as mg/kg food. The annex I of Regulation (EU) No 10/2011 on Plastic Materials and Articles has set out SMLs. If no SML is set, default limit 60 mg/kg food can be used for individual substances. Sometimes, total specific migration limit (SMLT) can be set for a group of similar substances. Its unit is also mg/kg food.
AP 89 1 - European Resolution BFR Federal Institute for Risk Assessment	The pigments used for pigments used for coloration comply with the requirements of the European Resolution AP (89) 1 or the German recommendation IX of BFR (Federal Institute for Risk Assessment. The printed surfaces shall not come into direct contact with food.
Regulation (EC) No 2023/2006	The product follows good manufacturing principles (gmp) according to Regulation (EC) No 2023/2006 when manufacturing these products.
Regulation (EC) No 1935/2004	Having regard to Regulation (EC) No 1935/2004 of the European Parliament and the Council of 27 October 2004 on materials and articles intended to come into contact with food (1), and in particular Article 5(1)

Tel.: +49 (0) 60 71 - 928 4000 Fax: +49 (0) 60 71 - 928 4019 E-Mail: <u>info@texit.de</u>

Gueterstrasse 2, DE-64807 Dieburg



Technical Data Sheet

Page 12 of 12

TMC-1154/TMC-1154

Tel.: +49 (0) 60 71 - 928 4000 Fax: +49 (0) 60 71 - 928 4019 E-Mail: <u>info@texit.de</u>

Related Standardards & Test Methods		
Document	Description	
HACCP approach Hazard analysis and critical control points	A systematic preventive approach to food safety from biological, chemical, physical hazards and more recently radiological hazards in production processes that can cause the finished product to be unsafe and designs measures to reduce these risks to a safe level. In this manner, HACCP attempts to avoid hazards rather than attempting to inspect finished products for the effects of those hazards. The HACCP system can be used at all stages of a food chain, from food production and preparation processes including packaging, distribution, etc. HACCP is focused only on the health safety issues of a product and not the quality of the product, yet HACCP principles are the basis of most food quality and safety assurance systems.	